



Halogen non-reflector

7158XHP 150W G6.35 24V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

产品数据

一般信息	
底盖	G6.35 [G6.35]
操作位置	S90 [直立 +/-90D 或底座朝下 (BDH)]
50% 故障条件下的使用寿命 (标称)	40 小时
灯技术	
相关色温 (标称)	3450 K
显色指数 (CRI)	100
操作和电气	
功耗	150 W
电压 (标称)	24 V
电压 (标称)	24 V
机械和外壳	
灯泡材料	开放紫外线石英

产品数据	
订单产品名称	7158XHP 150W G6.35 24V 1CT/10X10F
完整的产品名称	7158XHP 150W G6.35 24V 1CT/10X10F
完整产品代码	871150041020750
订购代码	924031720503
材料编号 (12NC)	924031720503
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500410207
计算器 - 每个外包装箱中的包数	100
EAN/UPC - 案例	8711500423221

Halogen non-reflector

二维绘图



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
7158XHP 150W	11.5 mm	31.5 mm	33.25	33	1.05 mm	1 mm	0.95	50 mm
G6.35 24V			mm	mm			mm	
1CT/10X10F								

