



# Halogen non-reflector

## 13701 110W G6.35 22.8V 1CT/10x10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

### Product data

General Information	
Cap-Base	G6.35 [G6.35]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	700 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	110 W
Voltage (Nom)	22.8 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	13701 110W G6.35 22.8V 1CT/10x10F
Full product name	13701 110W G6.35 22.8V 1CT/10x10F
Full product code	871150042826450
Order code	924031928303
Material Nr. (12NC)	924031928303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500428264
Numerator - Packs per outer box	100
EAN/UPC - Case	8711500428288

## Halogen non-reflector

### Dimensional drawing



Product	D (max)	L (min)	L (max)	L	C	P (max)	P	P (min)
13701 110W	11.7 mm	29.6 mm	30.4 mm	30	43 mm	1.05 mm	1 mm	0.95 mm
G6.35 22.8V				mm				
1CT/10x10F								

