



# Halogen non-reflector

## FLW 300W 24V 24PK

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


### Product data

General Information	
Cap-Base	GY6.35 [GY6.35]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	50 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3500 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	300 W
Voltage (Nom)	24 V
Voltage (Nom)	24 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	14530 300W GY6.35 24V 1CT/24
Full product name	FLW 300W 24V 24PK
Full product code	871150042461730
Order code	204925
Material Nr. (12NC)	924041420594
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500424617
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500424624

# Halogen non-reflector

## Dimensional drawing



Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
14530	9/16	1-5/16	1-5/16	1-5/16	1/16	1/16	1/16	2-3/16
300W	inch	inch	inch	inch	inch	inch	inch	inch
GY6.35 24V								
1CT/24								

