



Halogen reflector

EFR 150W 15V 50PK

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

Product data


General Information	
Cap-Base	GZ6.35 [GZ6.35]
Operating Position	P90/P15
Life to 50% Failures (Nom)	50 hour(s)
Light Technical	
Luminous Flux	840 lm
Correlated Color Temperature (Nom)	3380 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	15 V
Voltage (Nom)	15 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	-
Bulb Shape	R50 [R 50mm]
Product Data	
Order product name	6423FO 150W GZ6.35 15V 1CT/10X5F
Full product name	EFR 150W 15V 50PK
Full product code	871150040971360
Order code	314906
Material Nr. (12NC)	924048218504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500409713

Halogen reflector

Numerator - Packs per outer box	50
EAN/UPC - Case	8711500419231

Dimensional drawing



Product	D (max)	C (max)
6423FO 150W GZ6.35 15V 1CT/10X5F	50 mm	42 mm

