



Brilliantline Dichroic

Brilliantline Dichroic 20W GU5.3 12V MR16 36D 1CT/10X5F

Superior-quality low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 hour(s)
Switching Cycle	16,000
Rated Lifetime (Hours)	4,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	36 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	236 lm
Operating and Electrical	
Power Consumption	20.0 W
Lamp Current (Nom)	1.7 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Energy Consumption kWh/1000 h	21 kWh
Product Data	
Order product name	Brill 20W GU5.3 12V 36D 1CT/10X5F
Full product name	Brilliantline Dichroic 20W GU5.3 12V MR16 36D 1CT/10X5F
Full product code	871150042484660
Order code	42484660
Material Nr. (12NC)	924050217101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500424846
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500424860


Brilliantline Dichroic

Dimensional drawing



Product	D (max)	C (max)
Brill 20W GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

Photometric data



Light Distribution Diagram - Brill 20W GU5.3 12V 36D 1CT/10X5F

