



# Brilliantline Dichroic

## Brill 20W GU4 12V 30D 1CT/10X5F

Low-voltage, xenon gas-filled halogen burner with axial filament optically positioned in a glass reflector


### Product data

General Information	
Cap-Base	GU4 [GU4]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 hour(s)
Switching Cycle	16,000
Rated Lifetime (Hours)	4,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	30 degree(s)
Luminous Flux	215 lm
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	215 lm
Operating and Electrical	
Power Consumption	20.0 W
Lamp Current (Nom)	1.7 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR11 [1.375inch/35mm]
Approval and Application	
Energy Consumption kWh/1000 h	21 kWh
Product Data	
Order product name	Brill 20W GU4 12V 30D 1CT/10X5F
Full product name	Brill 20W GU4 12V 30D 1CT/10X5F
Full product code	871150042540960
Order code	924051317107
Material Nr. (12NC)	924051317107
Local order code	14625
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500425409
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500425423

Brilliantline Dichroic

Dimensional drawing



Product	D (max)	C (max)
Brill 20W GU4 12V 30D 1CT/10X5F	35 mm	40 mm

