



MASTERLine 111

MASTERLine 111 30W G53 12V 8D 1CT/6

Low-voltage halogen burner with very high energy efficiency and long lifetime thanks to IRR coating in decorative aluminum reflector equipped with ceramic anti-glare cap. Ideal solution for high-end modern luminaires, putting your objects in the spotlight. Aluminum coating prevents heat in the backlight.

Product data

| General Information | |
|------------------------|----------------------------------|
| Cap-Base | G53 [G53] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 4,000 hour(s) |
| Switching Cycle | 16,000 |
| Rated Lifetime (Hours) | 4,000 hour(s) |
| Lighting Technology | Halogen |

| Light Technical | |
|------------------------------------|-------------|
| Beam Angle (Nom) | 8 degree(s) |
| Correlated Color Temperature (Nom) | 3000 K |
| Color rendering index (CRI) | 100 |
| Luminous Flux in 90° Cone (Rated) | 325 lm |

| Operating and Electrical | |
|---------------------------|----------------------|
| Power Consumption | 30 W |
| Lamp Current (Nom) | 2.5 A |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 12 V |
| Voltage (Nom) | 12 V |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |


| Mechanical and Housing | |
|------------------------|----------------|
| Bulb Shape | R111 [R 111mm] |

| Approval and Application | |
|-------------------------------|--------|
| Energy Consumption kWh/1000 h | 32 kWh |

| Product Data | |
|---------------------------------|-------------------------------------|
| Order product name | MASTERLine 111 30W G53 12V 8D 1CT/6 |
| Full product name | MASTERLine 111 30W G53 12V 8D 1CT/6 |
| Full product code | 871150041101310 |
| Order code | 924058417161 |
| Material Nr. (12NC) | 924058417161 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500411013 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8711500437310 |

MASTERLine 111

Dimensional drawing



| Product | D (max) | C (max) | C1 (max) |
|-------------------------------------|---------|---------|----------|
| MASTERLine 111 30W G53 12V 8D 1CT/6 | 111 mm | 67 mm | 51 mm |

Photometric data



Light Distribution Diagram - MASTERLine 111 30W G53 12V 8D 1CT/6

