



# MASTERLine 111

## MASTERLine 111 60W G53 12V 24D 1CT/6

Low-voltage halogen reflector lamp with double-ended burner and high-purity aluminium reflector


### Product data

General Information	
Cap-Base	G53 [G53]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	4,000 hour(s)
Switching Cycle	16,000
Rated Lifetime (Hours)	4,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	24 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	840 lm
Operating and Electrical	
Power Consumption	60.0 W
Lamp Current (Nom)	5 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	R111 [R 111mm]
Approval and Application	
Energy Consumption kWh/1000 h	64 kWh
Product Data	
Order product name	MASTERLine 111 60W G53 12V 24D 1CT/6
Full product name	MASTERLine 111 60W G53 12V 24D 1CT/6
Full product code	871150041115010
Order code	924059017161
Material Nr. (12NC)	924059017161
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500411150
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500437365


MASTERLine 111

Dimensional drawing



Product	D (max)	C (max)	C1 (max)
MASTERLine 111 60W G53 12V 24D 1CT/6	111 mm	67 mm	51 mm

Photometric data



Light Distribution Diagram - MASTERLine 111 60W G53 12V 24D 1CT/6

