



# Appliance Oven Tubular

App 15W E14 230-240V T22 OV 1CT/10x10F

Tubular vacuum lamps with clear glass (T-bulb)

## Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	90 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	15,0 W
Lamp Current (Nom)	0.06 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T22 [T 22mm]
Approval and Application	
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Order product name	App 15W E14 230-240V T22 OV 1CT/10x10F
Full product name	App 15W E14 230-240V T22 OV 1CT/10x10F
Full product code	871869646658200
Order code	924196244402
Material Nr. (12NC)	924196244402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696466582
Numerator - Packs per outer box	100
EAN/UPC - Case	8718696466605

# Appliance Oven Tubular

## Dimensional drawing

Product	D (max)	C (max)
App 15W E14 230-240V T22 OV 1CT/10x10F	22 mm	49 mm

