



# Appliance Oven Tubular

## APP 15W E14 230-240V T22 CL OV 1CT

Tubular vacuum lamps with clear glass (T-bulb)

### Product data

General Information	
Cap base	E14 [E14]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 h
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 h
Lighting Technology	Incandescent
Flux measurement reference	Sphere

Light Technical	
Luminous Flux	85 lm
Chromaticity Coordinate X (Nom)	0.46
Chromaticity Coordinate Y (Nom)	0.411
Correlated Colour Temperature	2700 K
Colour rendering index (CRI)	100

Operating and Electrical	
Power Consumption	15.4 W
Lamp current (nom.)	0.06 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1

Voltage (nom.)	230-240 V
----------------	-----------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T22 [T 22 mm]

Approval and Application	
Energy Efficiency Class	G
Energy consumption kWh/1,000 hours	16 kWh
EPREL registration number	423229

Product Data	
Order product name	App 15W E14 230-240V T22 CL OV 1CT
Full product name	APP 15W E14 230-240V T22 CL OV 1CT
Full EOC	871150003659950
Order code	03659950
Material no. (12 NC)	924196244440
Local order code	15SESOZP
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500036599

## Appliance Oven Tubular

Numerator – packs per outer box	100
EAN/UPC - Case	8711500257673

### Dimensional drawing

Product	D (max)	C (max)
App 15W E14 230-240V T22 CL OV 1CT	22 mm	49 mm

