



# Appliance Oven Tubular

App 15W E14 230-240V T22 CL OV 1CT

Tubular vacuum lamps with clear glass (T-bulb)

## Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Flux measurement reference	Sphere

Light Technical	
Luminous Flux	85 lm
Chromaticity Coordinate X (Nom)	0.46
Chromaticity Coordinate Y (Nom)	0.411
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	15.4 W
Lamp Current (Nom)	0.06 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1

Voltage (Nom)	230-240 V
---------------	-----------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T22 [T 22mm]

Approval and Application	
Energy Efficiency Class	G
Energy Consumption kWh/1000 h	16 kWh
EPREL Registration Number	423229

Product Data	
Order product name	App 15W E14 230-240V T22 CL OV 1CT
Full product name	App 15W E14 230-240V T22 CL OV 1CT
Full product code	871150003659950
Order code	924196244440
Material Nr. (12NC)	924196244440
Local order code	OVEN15W235VSES
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500036599

Appliance Oven Tubular

Numerator - Packs per outer box	100
EAN/UPC - Case	8711500257673

Dimensional drawing

Product	D (max)	C (max)
App 15W E14 230-240V T22 CL OV 1CT	22 mm	49 mm

