



# Appliance Oven Tubular

App 15W E14 230-240V T22 CL OV 1BL/10

Tubular vacuum lamps with clear glass (T-bulb)

## Product data

| General Information                |                                  |
|------------------------------------|----------------------------------|
| Cap-Base                           | E14 [E14]                        |
| Operating Position                 | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime                   | 1,000 hour(s)                    |
| Switching Cycle                    | 4,000                            |
| Rated Lifetime (Hours)             | 1,000 hour(s)                    |
| Lighting Technology                | Incandescent                     |
| Light Technical                    |                                  |
| Luminous Flux                      | 90 lm                            |
| Correlated Color Temperature (Nom) | 2700 K                           |
| Color rendering index (CRI)        | 100                              |
| Operating and Electrical           |                                  |
| Power Consumption                  | 15.0 W                           |
| Lamp Current (Nom)                 | 0.06 A                           |
| Starting Time (Nom)                | 0.0 s                            |
| Warm-up time to 60% light          | instant full light s             |
| Power Factor (Fraction)            | 1                                |
| Voltage (Nom)                      | 230-240 V                        |
| Controls and Dimming               |                                  |
| Dimmable                           | Yes                              |

| Mechanical and Housing          |                                       |
|---------------------------------|---------------------------------------|
| Bulb Finish                     | Clear                                 |
| Bulb Shape                      | T22 [T 22mm]                          |
| Approval and Application        |                                       |
| Energy Consumption kWh/1000 h   | 15 kWh                                |
| Product Data                    |                                       |
| Order product name              | App 15W E14 230-240V T22 CL OV 1BL/10 |
| Full product name               | App 15W E14 230-240V T22 CL OV 1BL/10 |
| Full product code               | 871150003711425                       |
| Order code                      | 924196244451                          |
| Material Nr. (12NC)             | 924196244451                          |
| Numerator - Quantity Per Pack   | 1                                     |
| EAN/UPC - Product/Case          | 8711500037114                         |
| Numerator - Packs per outer box | 10                                    |
| EAN/UPC - Case                  | 8711500259103                         |

# Appliance Oven Tubular

## Dimensional drawing

| Product                               | D (max) | C (max) |
|---------------------------------------|---------|---------|
| App 15W E14 230-240V T22 CL OV 1BL/10 | 22 mm   | 49 mm   |

