



# Halogen High Voltage SE (Film/Studio)

1000W GX9.5 230V 1CT/10

Halogen High Voltage SE (Film/Studio) – stars on film and video The high, constant output and consistent colour temperature of these single ended halogen lamps ensure attractive, accurately exposed pictures for both film and video. What’s more, these lamps incorporate the highly innovative P3 technology, developed by Philips. This allows the lamps to be used at higher temperatures, which extends overall lifetime and consistency of their high-quality light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. In addition, the very wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.


## Product data

General Information	
Cap-Base	GX9.5 [GX9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	200 h
Light Technical	
Correlated Color Temperature (Nom)	3200 K
Operating and Electrical	
Power Consumption	1,000 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Order product name	1000W GX9.5 230V 1CT/10
Full product name	1000W GX9.5 230V 1CT/10
Full product code	871150050647425
Order code	924505144234
Material Nr. (12NC)	924505144234
Local order code	6995PP
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500506474
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500507501

# Halogen High Voltage SE (Film/Studio)

## Dimensional drawing



Product	D	H	W	L	C	P	P	R	K	K
	(max)				(max)	(max)	(min)		(max)	(min)
1000W	30.5	14.5	11	55	110 mm	3.25	3.10	9.53	9.2	8.4
GX9.5	mm	mm	mm	mm		mm	mm	mm	mm	mm
230V										
1CT/10										

