



Compact Source

6982P 800W G9.5 240V 1CT/10

The very compact filament in the Compact Source series helps create a proportionately high beam intensity and the Compact Source range is therefore ideal for the latest generation of high-performance luminaires. Also, thanks to their low energy consumption, each dimmer can serve significantly more fixtures, thereby reducing overall dimmer costs. What's more, the Compact Source lamps incorporate the innovative P3 technology, developed by Philips, which enables the lamps to be used at higher temperatures in any burning position. This results in longer lamp lifetimes, reduced lamp replacement costs, and a more consistent lighting performance over the whole lifetime of the lamp.


Product data

General Information	
Cap-Base	G9.5 [G9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	200 h
Light Technical	
Correlated Color Temperature (Nom)	3200 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	800 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Order product name	6982P 800W G9.5 240V 1CT/10
Full product name	6982P 800W G9.5 240V 1CT/10
Full product code	871150051937525
Order code	924545645528
Material Nr. (12NC)	924545645528
Local order code	6982P240V
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500519375
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500521613

Compact Source

Dimensional drawing



Product	D (max)	H	W	L	C (max)
6982P 800W G9.5 240V 1CT/10	19 mm	12.5 mm	9 mm	60.5 mm	104 mm

