



Hi-Brite

6980Z 1200W G22 80V 10PK


The compact, shock-resistant design of the Hi-Brite lamp series makes it easy to handle and ideal for moving head systems. Also, the compact filament ensures a high beam intensity, which can be used to reduce energy consumption: for example, 1200W can now be used instead of 2500W. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures in any burning position, which further extends lamp lifetime, reduces lamp replacement costs and ensures consistency of high-quality light output.

Product data

| General Information | |
|-----------------------------|----------------------------------|
| Cap-Base | G22 [G22] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Life to 50% Failures (Nom) | 200 hour(s) |
| Light Technical | |
| Color rendering index (CRI) | - |
| Operating and Electrical | |
| Power Consumption | 1,200 W |
| Voltage (Nom) | 80 V |
| Voltage (Nom) | 80 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|--------------------------|
| Bulb Finish | Clear |
| Product Data | |
| Full product code | 871150051946725 |
| Order product name | 6980Z 1200W G22 80V 10PK |
| Order code | 924546528928 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 10 |
| Material Nr. (12NC) | 924546528928 |
| Full product name | 6980Z 1200W G22 80V 10PK |
| EAN/UPC - Case | 8711500519498 |
| EAN/UPC - Product/Case | 8711500519467 |

Dimensional drawing



| Product | D (max) | H | W | L | C (max) |
|--------------------------|---------|---------|---------|---------|---------|
| 6980Z 1200W G22 80V 10PK | 25 mm | 10.2 mm | 11.7 mm | 63.5 mm | 140 mm |

