



Compact Source

6981P 750W G9.5 115V 1CT/10

The very compact filament in the Compact Source series helps create a proportionately high beam intensity and the Compact Source range is therefore ideal for the latest generation of high-performance luminaires. Also, thanks to their low energy consumption, each dimmer can serve significantly more fixtures, thereby reducing overall dimmer costs. What's more, the Compact Source lamps incorporate the innovative P3 technology, developed by Philips, which enables the lamps to be used at higher temperatures in any burning position. This results in longer lamp lifetimes, reduced lamp replacement costs, and a more consistent lighting performance over the whole lifetime of the lamp.


Product data

General Information	
Cap-Base	G9.5 [G9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	300 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3200 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	750 W
Voltage (Nom)	115 V
Voltage (Nom)	115 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Full product code	871150051957325
Order product name	6981P 750W G9.5 115V 1CT/10
Order code	924546834428
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924546834428
Full product name	6981P 750W G9.5 115V 1CT/10
EAN/UPC - Case	8711500519580
EAN/UPC - Product/Case	8711500519573

Compact Source

Dimensional drawing



Product	D (max)	H	W	L	C (max)
6981P 750W G9.5 115V 1CT/10	19 mm	9 mm	9.5 mm	60.5 mm	104 mm

