



Halogen High Voltage SE (Film/Studio)

7002Y 1000W G22 230V 1CT/10

The high, constant output and consistent color temperature of these single ended halogen lamps ensure attractive, accurately exposed pictures for both film and video. Furthermore, these lamps incorporate the highly innovative P3 technology, developed by Philips. This allows the lamps to be used at higher temperatures, which extends overall lifetime and consistency of their high-quality light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. In addition, the very wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.

Product data

General Information	
Cap-Base	G22 [G22]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	200 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3200 K
Operating and Electrical	
Power Consumption	1,000 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Full product code	871150018599025
Order product name	7002Y 1000W G22 230V 1CT/10
Order code	924553644228
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924553644228
Full product name	7002Y 1000W G22 230V 1CT/10
EAN/UPC - Case	8711500186003
EAN/UPC - Product/Case	8711500185990

Halogen High Voltage SE (Film/Studio)

Dimensional drawing

Product	D	H	W	L	C	P	P	R	K	K
	(max)				(max)	(max)	(min)		(max)	(min)
7002Y	22 mm	14	10.5	72.5	140	6.40	6.30	22.22	26.54	24.89
1000W		mm	mm	mm	mm	mm	mm	mm	mm	mm
G22 230V										
1CT/10										

