



HPL

7007 575W Heat Sink 115V 1CT/10

HPL lamps include a barrel-shaped filament that is approved by ETC for use in its Source Four™ fixtures. Bright, high quality light and high beam intensity is assured by the optimal filament design, while the unique P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which extends lifetime and consistency of high-quality light output, resulting in fewer early failures and fewer maintenance man hour costs.

Product data

| General Information | |
|----------------------------|----------------------------------|
| Cap-Base | HEATSINK [Heat Sink] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Life to 50% Failures (Nom) | 300 hour(s) |

| Light Technical | |
|------------------------------------|--------|
| Correlated Color Temperature (Nom) | 3200 K |
| Color rendering index (CRI) | 100 |


| Operating and Electrical | |
|--------------------------|-------|
| Power Consumption | 575 W |
| Voltage (Nom) | 115 V |
| Voltage (Nom) | 115 V |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|-------|
| Bulb Finish | Clear |

| Product Data | |
|---------------------------------|---------------------------------|
| Full product code | 871150018525925 |
| Order product name | 7007 575W Heat Sink 115V 1CT/10 |
| Order code | 924554934428 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 10 |
| Material Nr. (12NC) | 924554934428 |
| Full product name | 7007 575W Heat Sink 115V 1CT/10 |
| EAN/UPC - Case | 8711500185402 |
| EAN/UPC - Product/Case | 8711500185259 |

Dimensional drawing



| Product | D (max) | H | W | D1 | L | C (max) |
|---------------------------------|---------|------|------|------|---------|---------|
| 7007 575W Heat Sink 115V 1CT/10 | 19 mm | 9 mm | 6 mm | 6 mm | 60.3 mm | 104 mm |

