



# HPL

## 7007 575W Heat Sink 240V 1CT/10

HPL lamps include a barrel-shaped filament that is approved by ETC for use in its Source Four™ fixtures. Bright, high quality light and high beam intensity is assured by the optimal filament design, while the unique P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which extends lifetime and consistency of high-quality light output, resulting in fewer early failures and fewer maintenance man hour costs.

### Product data

General Information	
Cap-Base	HEATSINK [Heat Sink]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	400 h

Light Technical	
Correlated Color Temperature (Nom)	3200 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	575 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear

Product Data	
Order product name	7007 575W Heat Sink 240V 1CT/10
Full product name	7007 575W Heat Sink 240V 1CT/10
Full product code	871150018531025
Order code	924554945528
Material Nr. (12NC)	924554945528
Local order code	HPL575240SL
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500185310
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500185426

Dimensional drawing



Product	D (max)	H	W	D1	L	C (max)
7007 575W Heat Sink 240V 1CT/10	19 mm	10 mm	8.6 mm	7.5 mm	60.3 mm	104 mm

