



HPL

7007/LL 575W Heat Sink 115V 1CT/10

HPL lamps include a barrel-shaped filament that is approved by ETC for use in its Source Four™ fixtures. Bright, high quality light and high beam intensity is assured by the optimal filament design, while the unique P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which extends lifetime and consistency of high-quality light output, resulting in fewer early failures and fewer maintenance man hour costs.

Product data

General Information	
Cap-Base	HEATSINK [Heat Sink]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	2,000 hour(s)

Light Technical	
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100


Operating and Electrical	
Power Consumption	575 W
Voltage (Nom)	115 V
Voltage (Nom)	115 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear

Product Data	
Full product code	871150018534125
Order product name	7007/LL 575W Heat Sink 115V 1CT/10
Order code	924555034428
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924555034428
Full product name	7007/LL 575W Heat Sink 115V 1CT/10
EAN/UPC - Case	8711500185433
EAN/UPC - Product/Case	8711500185341

Dimensional drawing



Product	D (max)	H	W	D1	L	C (max)
7007/LL 575W Heat Sink 115V 1CT/10	19 mm	11 mm	6 mm	6 mm	60.3 mm	104 mm

