



# HPL

## 7007/LL 575W Heat Sink 230V 1CT/10


HPL lamps include a barrel-shaped filament that is approved by ETC for use in its Source Four™ fixtures. Bright, high quality light and high beam intensity is assured by the optimal filament design, while the unique P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which extends lifetime and consistency of high-quality light output, resulting in fewer early failures and fewer maintenance man hour costs.

### 产品数据

一般信息	
底盖	HEATSINK [Heat Sink]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	1,500 小时
灯技术	
相关色温 (标称)	3000 K
显色指数 (CRI)	100
操作和电气	
功耗	575 W
电压 (标称)	230 V
电压 (标称)	230 V
控制和调光	
可调光	是

机械和外壳	
灯泡外观	透明
产品数据	
订单产品名称	7007/LL 575W Heat Sink 230V 1CT/10
完整的产品名称	7007/LL 575W Heat Sink 230V 1CT/10
完整产品代码	871150018535825
订购代码	924555044228
材料编号 (12NC)	924555044228
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500185358
计算器 - 每个外包装箱中的包数	10
EAN/UPC - 案例	8711500185464

## 二维绘图



Product	D (max)	H	W	D1	L	C (max)
7007/LL 575W Heat Sink 230V	19 mm	11.5 mm	8.6 mm	7.5 mm	60.3 mm	104 mm
1CT/10						

