



# HPL

## 7007/LL 575W HEAT SINK 240V 1CT/10


HPL lamps include a barrel-shaped filament that is approved by ETC for use in its Source Four™ fixtures. Bright, high quality light and high beam intensity is assured by the optimal filament design, while the unique P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which extends lifetime and consistency of high-quality light output, resulting in fewer early failures and fewer maintenance man hour costs.

### Product data

General Information	
Cap-Base	HEATSINK [Heat Sink]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	1,500 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	575 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Product Data	
Order product name	7007/LL 575W Heat Sink 240V 1CT/10
Full product name	7007/LL 575W HEAT SINK 240V 1CT/10
Full product code	871150018536525
Order code	18536525
Material Nr. (12NC)	924555045528
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500185365
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500185471

Dimensional drawing



Product	D (max)	H	W	D1	L	C (max)
7007/LL 575W Heat Sink 240V	19 mm	11.5 mm	9.2 mm	8 mm	60.3 mm	104 mm
1CT/10						

