



# Plusline Compact

DE 220-230V150W

Mains-voltage linear lamp giving white halogen light


## Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	2,400 lumen
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	16 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Lamp Current (Nom)	0.65 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]
Product Data	
Full product code	871150099323600
Order product name	DE 220-230V150W
Order code	924571443380
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	924571443380
Full product name	DE 220-230V150W
EAN/UPC - Case	8711500993274
EAN/UPC - Product/Case	8711500993236

Plusline Compact

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
DE 220-230V150W	12 mm	76.5 mm	74.9 mm	73.3 mm	78.3 mm

