



# Plusline ES Small

## Plusline 118mm 2y 240W R7s 230V 1BB

Mains-voltage halogen linear lamp with superior quality and reliability. Offers very long lifetime and crisp halogen light. Ideal solution for decorative luminaires and for security or task lighting floodlights.

### Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	4,900 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	20.4 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	240.0 W
Lamp Current (Nom)	1.04 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11 [T 11mm]


Approval and Application	
Energy Consumption kWh/1000 h	240 kWh

Product Data	
Order product name	Plusline 118mm 2y 240W R7s 230V 1BB
Full product name	Plusline 118mm 2y 240W R7s 230V 1BB
Full product code	872790085380300
Order code	924572044210
Material Nr. (12NC)	924572044210
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900853803
Numerator - Packs per outer box	100
EAN/UPC - Case	8727900853827

## Plusline ES Small

### Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline 118mm 2y 240W R7s 230V 1BB	11 mm	115.8 mm	114.2 mm	112.6 mm	118 mm

