



# Halogen FastFit

## Hi-Brite 7016G 1200W 80V FastFit

Halogen FastFit lamps are replaced in seconds - thanks to the specially designed base. The compact filament ensures high beam intensity, while the shock-resistant design allows easy handling and reliable use in moving head systems. In addition, the highly innovative P3 technology allows use at higher temperatures, which further extends lifetime and consistency of light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. And because the FastFit design is also applied to Philips MSR/MSD Gold™ lamps, switching lamp technologies is also quick and easy.

### Product data

General Information	
Cap-Base	PGJX50 [ PGJX50]
Philips Code	7016G
ANSI Code	-
Operating Position	UNIVERSAL [ Any or Universal (U)]
Main Application	Entertainment
Life to 50% Failures (Nom)	200 h
System Description	P3 Technology
Light Technical	
Luminous Flux (Rated) (Nom)	36000 lm
Correlated Color Temperature (Nom)	3250 K
Operating and Electrical	
Power (Rated) (Nom)	1200 W
Rapid Acting HBC Fuse	16 V
Voltage (Nom)	80 V


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Filament Shape	Bi-Plane
Filament Dimensions WxH	12x10.5
Luminaire Design Requirements	
Pinch Temperature (Max)	500 °C
Product Data	
Full product code	871150050707525
Order product name	Hi-Brite 7016G 1200W 80V FastFit
EAN/UPC - Product	8711500507075
Order code	924575228928
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924575228928

## Halogen FastFit

Net Weight (Piece)

0.139 kg

### Dimensional drawing



Product	D (max)	H	W	L	C (max)	E (max)
Hi-Brite 7016G 1200W 80V FastFit	25 mm	10.5 mm	11.7 mm	82 mm	140 mm	41 mm

Hi-Brite 7016G 1200W PGJX50 80V FastFit

