



Halogen FastFit

Hi-Brite 7017G 750W 80V FastFit

Halogen FastFit lamps are replaced in seconds – thanks to the specially designed base. The compact filament ensures high beam intensity, while the shock-resistant design allows easy handling and reliable use in moving head systems. In addition, the highly innovative P3 technology allows use at higher temperatures, which further extends lifetime and consistency of light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. And because the FastFit design is also applied to Philips MSR/MSD Gold™ lamps, switching lamp technologies is also quick and easy.


Product data

General Information	
Cap-Base	PGJX50 [PGJX50]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	300 hour(s)
Operating and Electrical	
Power Consumption	750 W
Voltage (Nom)	80 V
Voltage (Nom)	80 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear

Product Data	
Full product code	871150050795225
Order product name	Hi-Brite 7017G 750W 80V FastFit
Order code	924576828928
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	924576828928
Full product name	Hi-Brite 7017G 750W 80V FastFit
EAN/UPC - Case	8711500507969
EAN/UPC - Product/Case	8711500507952

Halogen FastFit

Dimensional drawing



Product	D (max)	H	W	L	C (max)	E (max)
Hi-Brite 7017G 750W 80V FastFit	19 mm	10 mm	8.5 mm	65 mm	125 mm	41 mm

