



Halogen FastFit

7018G 800W PGJX50 230V FastFit


Halogen FastFit lamps are replaced in seconds – thanks to the specially designed base. The compact filament ensures high beam intensity, while the shock-resistant design allows easy handling and reliable use in moving head systems. In addition, the highly innovative P3 technology allows use at higher temperatures, which further extends lifetime and consistency of light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. And because the FastFit design is also applied to Philips MSR/MSD Gold™ lamps, switching lamp technologies is also quick and easy.

Product data

General Information		Mechanical and Housing	
Cap-Base	PGJX50 [PGJX50]	Bulb Finish	Clear
Operating Position	UNIVERSAL [Any or Universal (U)]	Product Data	
Life to 50% Failures (Nom)	150 hour(s)	Full product code	872790080737000
Light Technical		Order product name	7018G 800W PGJX50 230V FastFit
Correlated Color Temperature (Nom)	3200 K	Order code	924582344228
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	800 W	Numerator - Packs per outer box	10
Voltage (Nom)	230 V	Material Nr. (12NC)	924582344228
Voltage (Nom)	230 V	Full product name	7018G 800W PGJX50 230V FastFit
Controls and Dimming		EAN/UPC - Case	8727900807387
Dimmable	Yes	EAN/UPC - Product/Case	8727900807370

Halogen FastFit

Dimensional drawing



Product	D (max)	H	W	L	C (max)	E (max)
7018G 800W PGJX50 230V FastFit	19 mm	12.5 mm	9 mm	79 mm	140 mm	41 mm

