



Plusline ES Compact

Plusline 78mm 2y 120W R7s 230V 1BB

Mains-voltage halogen linear lamp with superior quality and reliability. Offers very long lifetime and crisp halogen light. Ideal solution for decorative luminaires.

Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	2,220 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	18.5 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	120 W
Lamp Current (Nom)	0.52 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11 [T 11mm]

Approval and Application	
Energy Consumption kWh/1000 h	120 kWh

Product Data	
Order product name	Plusline 78mm 2y 120W R7s 230V 1BB
Full product name	Plusline 78mm 2y 120W R7s 230V 1BB
Full product code	872790085223300
Order code	924587244210
Material Nr. (12NC)	924587244210
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900852233
Numerator - Packs per outer box	100
EAN/UPC - Case	8727900852257

Plusline ES Compact

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline 78mm 2y 120W R7s 230V 1BB	11 mm	76.5 mm	74.9 mm	73.3 mm	78 mm

