



HalogenA PAR20

PAR20 HAL 50W E27 120V 25D 1CT/15

Mains-voltage halogen reflector that is easy to install instead of conventional reflector lamps, putting your objects in a superior-quality spot light. Provides crisp halogen light over a long lifetime.


Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 hour(s)
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	25 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR20 [PAR 2.5 inch/63mm]
Product Data	
Order product name	PAR20 HAL 50W E27 120V 25D 1CT/15
Full product name	PAR20 HAL 50W E27 120V 25D 1CT/15
Full product code	871150088775700
Order code	924710336383
Material Nr. (12NC)	924710336383
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500887757
Numerator - Packs per outer box	15
EAN/UPC - Case	8711500887818


HalogenA PAR20

Dimensional drawing



Product	D (max)	C (max)
PAR20 HAL 50W E27 120V 25D 1CT/15	63.5 mm	105 mm

Photometric data



Light Distribution Diagram - PAR20 HAL 50W E27 120V 25D 1CT/15

