



Twistline Alu 2000 hours

Tw Alu 2000h 35W GU10 240V 40D 1CT/50

Mains-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in a superior-quality spot light. Aluminum coating prevents heat in the backlight.

Product data

General Information		Voltage (Nom)	
Cap-Base	GU10 [GU10]	240 V	
Operating Position	UNIVERSAL [Any or Universal (U)]	Controls and Dimming	
Nominal lifetime	2,000 hour(s)	Dimmable	Yes
Switching Cycle	4,000	Mechanical and Housing	
Rated Lifetime (Hours)	2,000 hour(s)	Bulb Finish	Clear
Lighting Technology	Halogen	Bulb Shape	MR16 [2inch/50mm]
Light Technical		Approval and Application	
Beam Angle (Nom)	40 degree(s)	Energy Consumption kWh/1000 h	35 kWh
Correlated Color Temperature (Nom)	2800 K	Product Data	
Color rendering index (CRI)	100	Order product name	Tw Alu 2000h 35W GU10 240V 40D 1CT/50
Luminous Flux in 90° Cone (Rated)	185 lm	Full product name	Tw Alu 2000h 35W GU10 240V 40D 1CT/50
Operating and Electrical		Full product code	871150065280565
Power Consumption	35.0 W	Order code	924713445555
Starting Time (Nom)	0.0 s	Material Nr. (12NC)	924713445555
Warm-up time to 60% light	instant full light s	Numerator - Quantity Per Pack	1
Power Factor (Fraction)	1	EAN/UPC - Product/Case	8711500652805
Voltage (Nom)	240 V	Numerator - Packs per outer box	50

Twistline Alu 2000 hours

EAN/UPC - Case

8711500652829

Dimensional drawing

Product	D (max)	C (max)
Tw Alu 2000h 35W GU10 240V 40D 1CT/50	50.7 mm	51 mm

