



Twistline Alu 2000 hours

Hal-Twist 2y 50W GU10 230V 40D 1CT/10X5F

Mains-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in a superior-quality spot light. Aluminum coating prevents heat in the backlight.

Product data


| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | GU10 [GU10] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 2,000 hour(s) |
| Switching Cycle | 8,000 |
| Rated Lifetime (Hours) | 2,000 hour(s) |
| Lighting Technology | Halogen |
| | |
| Light Technical | |
| Beam Angle (Nom) | 40 degree(s) |
| Correlated Color Temperature (Nom) | 2800 K |
| Color rendering index (CRI) | 100 |
| Luminous Flux in 90° Cone (Rated) | 330 lm |
| | |
| Operating and Electrical | |
| Power Consumption | 50.0 W |
| Starting Time (Nom) | 0.0 s |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction) | 1 |
| Voltage (Nom) | 230 V |

| Voltage (Nom) | 230 V |
|---------------------------------|--|
| | |
| Controls and Dimming | |
| Dimmable | Yes |
| | |
| Mechanical and Housing | |
| Bulb Finish | Clear |
| Bulb Shape | MR16 [2inch/50mm] |
| | |
| Approval and Application | |
| Energy Consumption kWh/1000 h | 50 kWh |
| | |
| Product Data | |
| Order product name | Hal-Twist 2y 50W GU10 230V 40D 1CT/10X5F |
| Full product name | Hal-Twist 2y 50W GU10 230V 40D 1CT/10X5F |
| Full product code | 871150041258460 |
| Order code | 924713544235 |
| Material Nr. (12NC) | 924713544235 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500412584 |
| Numerator - Packs per outer box | 50 |

Twistline Alu 2000 hours

| | |
|----------------|---------------|
| EAN/UPC - Case | 8711500412607 |
|----------------|---------------|

Dimensional drawing



| Product | D (max) | C (max) |
|--|---------|---------|
| Hal-Twist 2y 50W GU10 230V 40D 1CT/10X5F | 50.7 mm | 51 mm |

