



Twistline Alu 2000 hours

Twistline Alu 2000h 50W GU10 240V 40D 1CT/10X5F

Mains-voltage 50 mm diameter reflector lamp with aluminium reflector

Product data

General Information	
Cap base	GU10 [GU10]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 h
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 h
Lighting Technology	Halogen

Light Technical	
Beam angle (nom.)	40 degree(s)
Correlated Colour Temperature	2800 K
Colour rendering index (CRI)	100
Luminous flux in 90° cone (rated)	330 lm

Operating and Electrical	
Power Consumption	50.0 W
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (nom.)	240 V
Voltage (nom.)	240 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	MR16 [2 inch/50 mm]

Approval and Application	
Energy consumption kWh/1,000 hours	50 kWh

Product Data	
Order product name	Tw Alu 2000h 50W GU10 240V 40D 1CT/10X5F
Full product name	Twistline Alu 2000h 50W GU10 240V 40D 1CT/10X5F
Full EOC	871150042856160
Order code	42856160
Material no. (12 NC)	924713545525
Local order code	18045
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500428561
Numerator – packs per outer box	50
EAN/UPC – Case	8711500428585

Twistline Alu 2000 hours

Dimensional drawing



Product	D (max)	C (max)
Tw Alu 2000h 50W GU10 240V 40D 1CT/10X5F	50.7 mm	51 mm

