



Plusline Small

Plusline S 300W R7s 240V 1CT/10X10F

Mains-voltage linear lamp giving white halogen light

Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	5,114 lm
Luminous Efficacy (rated) (Nom)	17 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	300 W
Lamp Current (Nom)	1.25 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	240 V
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]
Product Data	
Order product name	Plusline S 300W R7s 240V 1CT/10X10F
Full product name	Plusline S 300W R7s 240V 1CT/10X10F
Full product code	872790080899500
Order code	924735445522
Material Nr. (12NC)	924735445522
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900808995
Numerator - Packs per outer box	100
EAN/UPC - Case	8727900809008

Plusline Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline S 300W R7s 240V 1CT/ 10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

