



# PAR16

## 60PAR16/HAL/FL27 120V 15PK

Philips Halogen PAR lamps will provide bright, white light across the product line and feature excellent beam qualities for accent or ambient lighting. Their optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering, making it easy to optimize the look and feel of your store and your merchandise.


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	27 degree(s)
Luminous Flux	580 lm
Luminous Intensity (Nom)	1,800 cd
Correlated Color Temperature (Nom)	2900 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Reflector Finish	Aluminized
Bulb Shape	PAR16 [PAR 2 inch/50mm]
Product Data	
Order product name	60PAR16/HAL/FL27 120V 15PK
Full product name	60PAR16/HAL/FL27 120V 15PK
Order code	924757103607
Material Nr. (12NC)	924757103607
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677330064
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677330069

## PAR16

### Dimensional drawing



#### Product

60PAR16/HAL/FL27 120V 15PK

