



Essential MV MR16 Alu

ESS MR16 50W GU10 230V 40D 1CT/10X5F

The Essential MV MR16 Alu is part of the Philips "Value for Money" ranges. It is ideal for professional end-users looking for accent light - without a transformer - to create contrast in shops, hotels and restaurants.


Product data

General Information	
Cap-Base	GU10 [GU10]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	40 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	50 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16 [2inch/50mm]
Product Data	
Order product name	ESS MR16 50W GU10 230V 40D 1CT/10X5F
Full product name	ESS MR16 50W GU10 230V 40D 1CT/10X5F
Full product code	871150088793100
Order code	924782744283
Material Nr. (12NC)	924782744283
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500887931
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500887962

Essential MV MR16 Alu

Dimensional drawing



Product	D (max)	C (max)
ESS MR16 50W GU10 230V 40D 1CT/10X5F	51 mm	51 mm

