



PAR56 and PAR64

PAR64 1000W 240V NSP

These self-contained spotlights are ideal for intensifying the visual experience in all kinds of clubs, that is because their accurate beam control picks out even the smallest of details even over long distances. This beam control makes the PAR 56 and PAR 64 excellent for long-range light projections. In addition, the universal burning feature provides complete flexibility of luminaires angle and position, while the front glass of the PAR56 provides thermal and physical protection. The result? Complete creative freedom to achieve the desired effect. Immediate re-strike also ensures instant resumption of entertainment after any power interruption.


产品数据

一般信息	
底盖	GX16D [GX16d]
操作位置	UNIVERSAL [任意或通用 (U)]
标称使用寿命	300 小时
灯技术	
光束角度 (标称)	12 °
相关色温 (标称)	3200 K
操作和电气	
功耗	1,000 W
电压 (标称)	240 V
电压 (标称)	240 V
控制和调光	
可调光	是

机械和外壳	
灯泡外形	PAR64 [PAR 8 英寸/200 毫米]
产品数据	
订单产品名称	PAR64 1000W 240V NSP
完整的产品名称	PAR64 1000W 240V NSP
完整产品代码	871150044072310
订购代码	924783345504
材料编号 (12NC)	924783345504
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500440723
计算器 - 每个外包装箱中的包数	6
EAN/UPC - 案例	8711500440730

PAR56 and PAR64

二维绘图



Product	D (max)	C (max)
PAR64 1000W 240V NSP	204 mm	150 mm

