



# D.C. Bayonet

## 100Q/CL/DC ESR 120V 12PK

Accent lighting with improved lumens and higher performance. Halogen DC Bayonett Capsule lamps provide bright, white light for decorative and accent lighting and general illumination. Offered in T4 bulb size with DC Bayonette base configurations. These lamps offer a rated average life ranging from 1000 to 2000 hours depending upon the product. \* \* Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

### Product data

General Information	
Cap-Base	BA15D [BA15d]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	1,900 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	100 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Standard Quartz
Bulb Shape	T-4
Product Data	
Order product name	DCBAY 100W 120V ESR 1CT/12
Full product name	100Q/CL/DC ESR 120V 12PK
Order code	442780
Material Nr. (12NC)	924794736381
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677115074
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677115079

D.C. Bayonet

Dimensional drawing

Product
DCBAY 100W 120V ESR 1CT/12

