



Halogen Low Voltage

13163 ELC/5H 250W GX5.3 24V 1CT/24

The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.

Product data

| General Information | |
|-----------------------------|--|
| Cap-Base | GX5.3 [GX5.3] |
| Operating Position | S90 [Standing +/-90D or Base Down (BDH)] |
| Life to 50% Failures (Nom) | 500 h |
| Light Technical | |
| Color rendering index (CRI) | 100 |
| Operating and Electrical | |
| Power Consumption | 250 W |
| Voltage (Nom) | 24 V |
| Voltage (Nom) | 24 V |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb Material | Quartz-UV Open |

| Reflector Finish | Smooth |
|---------------------------------|------------------------------------|
| Bulb Shape | R50 [R 50mm] |
| Product Data | |
| Order product name | 13163 ELC/5H 250W GX5.3 24V 1CT/24 |
| Full product name | 13163 ELC/5H 250W GX5.3 24V 1CT/24 |
| Full product code | 871150041347530 |
| Local code description | 131635H |
| Order code | 924862720540 |
| Material Nr. (12NC) | 924862720540 |
| Local order code | 131635H |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500413475 |
| Numerator - Packs per outer box | 24 |
| EAN/UPC - Case | 8711500435736 |

Halogen Low Voltage

Dimensional drawing



| Product | D (max) | C (max) |
|------------------------------------|---------|---------|
| 13163 ELC/5H 250W GX5.3 24V 1CT/24 | 50 mm | 44.5 mm |

