



Halogen Low Voltage

13163 ELC/5H 250W GX5.3 24V 1CT/24

The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.


产品数据

一般信息	
底盖	GX5.3 [GX5.3]
操作位置	S90 [直立 +/-90D 或底座朝下 (BDH)]
50% 故障条件下的使用寿命 (标称)	500 小时
灯技术	
显色指数 (CRI)	100
操作和电气	
功耗	250 W
电压 (标称)	24 V
电压 (标称)	24 V
控制和调光	
可调光	是
机械和外壳	
灯泡材料	开放紫外线石英

反射器外观	光滑
灯泡外形	R50 [R 50 毫米]
产品数据	
订单产品名称	13163 ELC/5H 250W GX5.3 24V 1CT/24
完整的产品名称	13163 ELC/5H 250W GX5.3 24V 1CT/24
完整产品代码	871150041347530
订购代码	924862720540
材料编号 (12NC)	924862720540
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500413475
计算器 - 每个外包装箱中的包数	24
EAN/UPC - 案例	8711500435736

Halogen Low Voltage

二维绘图



Product	D (max)	C (max)
13163 ELC/5H 250W GX5.3 24V 1CT/24	50 mm	44.5 mm

