



Twistline Alu 2000 hours

TWIST ALU 25W GU10 230V 25D 1CT/10x5F

Mains-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in a superior-quality spot light. Aluminum coating prevents heat in the backlight.

Product data

General Information	
Cap-Base	GU10 [GU10]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	25 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	130 lm
Operating and Electrical	
Power Consumption	25.0 W
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V

Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Energy Consumption kWh/1000 h	25 kWh
Product Data	
Order product name	TWIST ALU 25W GU10 230V 25D 1CT/10x5F
Full product name	TWIST ALU 25W GU10 230V 25D 1CT/10x5F
Full product code	871150065239365
Order code	924887044213
Material Nr. (12NC)	924887044213
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500652393
Numerator - Packs per outer box	50


Twistline Alu 2000 hours

EAN/UPC - Case	8711500652416
----------------	---------------

Dimensional drawing

Product	D (max)	C (max)
TWIST ALU 25W GU10 230V 25D 1CT/10x5F	50.7 mm	51 mm

Photometric data



Light Distribution Diagram - TWIST ALU 25W GU10 230V 25D 1CT/10x5F

