



# Twistline GU10

## BC25 TWISTLINE GU10 / FL25

Bright, white accent light with superior energy savings. Philips Twistline GU10 Philips Halogen Twistline MR16 with GU10 base provide bright white accent light. The twist and lock base enables easy installation and a secure fit. Suited for track and recessed lighting applications.


### Product data

General Information	
Cap-Base	GU10 [GU10]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	25 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	25 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16 [2inch/50mm]
Product Data	
Order product name	BC25 TWISTLINE GU10 / FL25
Full product name	BC25 TWISTLINE GU10 / FL25
Order code	924887736301
Material Nr. (12NC)	924887736301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677416935
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677416930


Twistline GU10

Dimensional drawing



Product	D (max)	C (max)
BC25 TWISTLINE GU10 / FL25	50.7 mm	53 mm

Photometric data



Light Distribution Diagram - BC25 TWISTLINE GU10 / FL25

