



MR16

BC50MRC16/SP10 EXT 12/1 TP

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	3,000 hour(s)
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Beam Angle (Nom)	10 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	50 W
Lamp Current (Nom)	4.17 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Voltage (Nom)	12 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Product Data	
Order product name	BC50MRC16/SP10 EXT 12/1 TP
Full product name	BC50MRC16/SP10 EXT 12/1 TP
Order code	415638
Material Nr. (12NC)	924888717101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677415631
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677415636

MR16

Dimensional drawing



Product	D (max)	C (max)
BC50MRC16/SP10 EXT 12/1 TP	2-1/16 inch	1-13/16 inch

