



# Reflector Flood

45R20 130V 12/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


## Product data

| General Information      |                                   |
|--------------------------|-----------------------------------|
| Cap-Base                 | E26 [Single Contact Medium Screw] |
| Operating Position       | UNIVERSAL [Any or Universal (U)]  |
| Rated Lifetime (Hours)   | 2,000 hour(s)                     |
| Lighting Technology      | Incandescent                      |
| Light Technical          |                                   |
| Luminous Flux            | 380 lm                            |
| Operating and Electrical |                                   |
| Power Consumption        | 45 W                              |
| Voltage (Nom)            | 130 V                             |
| Voltage (Nom)            | 130 V                             |
| Mechanical and Housing   |                                   |
| Bulb Finish              | Frosted                           |

| Bulb Shape                      | R20 [R 63mm]    |
|---------------------------------|-----------------|
| Product Data                    |                 |
| Order product name              | 45R20 130V 12/1 |
| Full product name               | 45R20 130V 12/1 |
| Order code                      | 925154436103    |
| Material Nr. (12NC)             | 925154436103    |
| Numerator - Quantity Per Pack   | 1               |
| EAN/UPC - Product/Case          | 046677203221    |
| Numerator - Packs per outer box | 12              |
| EAN/UPC - Case                  | 50046677203226  |

# Reflector Flood

## Dimensional drawing



| Product         | C (max)   |
|-----------------|-----------|
| 45R20 130V 12/1 | 3.94 inch |

