



# DuraMax Reflector Flood

45R20/LL 120V 12/1

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.


## Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,500 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	385 lumen
Operating and Electrical	
Power Consumption	45 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	R20 [R 63mm]
Product Data	
Order product name	45R20/LL 120V 12/1
Order code	925154636304
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	925154636304
Full product name	45R20/LL 120V 12/1
EAN/UPC - Case	50046677203233
EAN/UPC - Product/Case	046677203238

# DuraMax Reflector Flood

## Dimensional drawing



Product	D	C (max)
45R20/LL 120V 12/1	2.5 inch	3.94 inch

