



DuraMax Reflector Flood

45BR30/FL55/LL 120V 12/1 TP

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	H90 [Hanging +/-90D or Base Up HOR (BUH)]
Nominal lifetime	2,500 hour(s)
Rated Lifetime (Hours)	2,500 hour(s)
Lighting Technology	Incandescent
Light Technical	
Beam Angle (Nom)	55 degree(s)
Luminous Flux	330 lm
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	45 W
Warm-up time to 60% light	instant full light s
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR30
Product Data	
Order product name	45BR30/FL55/LL 120V 12/1 TP
Full product name	45BR30/FL55/LL 120V 12/1 TP
Order code	925179636308
Material Nr. (12NC)	925179636308
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677167516
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677167511

DuraMax Reflector Flood

Dimensional drawing



Product

45BR30/FL55/LL 120V 12/1 TP

