



Rough / Vibration Service

300/IF 120/130V 12/1


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux (Max)	4,025 lm
Luminous Flux	5,700 lm
Operating and Electrical	
Power Consumption	300 W
Voltage (Nom)	120-130 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	PS35
Product Data	
Order product name	300/IF 120/130V 12/1
Full product name	300/IF 120/130V 12/1
Order code	143164
Material Nr. (12NC)	925268434302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677143169
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677143164

Dimensional drawing



Product
300/IF 120/130V 12/1

