



# Rough / Vibration Service

300/IF 120/130V 12/1


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Rough Service incandescent lamps have an exceptionally strong filament for which a special filament wire is used, which makes these lamps extremely suitable for places where shocks, bumps and vibrations frequently occur. The clear version, with its completely visible filament, is a brilliant light source, whereas the inside-frosted lamp is used wherever well diffused light is required.

## Product data

| General Information      |                                  |
|--------------------------|----------------------------------|
| Cap-Base                 | E39 [Single Contact Mogul Screw] |
| Operating Position       | UNIVERSAL [Any or Universal (U)] |
| Rated Lifetime (Hours)   | 1,000 hour(s)                    |
| Lighting Technology      | Incandescent                     |
| Light Technical          |                                  |
| Luminous Flux (Max)      | 4,025 lumen                      |
| Luminous Flux            | 5,700 lumen                      |
| Operating and Electrical |                                  |
| Power Consumption        | 300 W                            |
| Voltage (Nom)            | 120-130 V                        |
| Mechanical and Housing   |                                  |
| Bulb Finish              | Frosted                          |

| Bulb Shape                      | PS35                 |
|---------------------------------|----------------------|
| Product Data                    |                      |
| Order product name              | 300/IF 120/130V 12/1 |
| Order code                      | 925268434302         |
| Numerator - Quantity Per Pack   | 1                    |
| Numerator - Packs per outer box | 12                   |
| Material Nr. (12NC)             | 925268434302         |
| Full product name               | 300/IF 120/130V 12/1 |
| EAN/UPC - Case                  | 50046677143164       |
| EAN/UPC - Product/Case          | 046677143169         |

Dimensional drawing



| Product              |
|----------------------|
| 300/IF 120/130V 12/1 |

