



Reflector Infrared R40

250R40 IR/HR/TG 120V 4/1


Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. Philips Infrared lamps are suited for heating and drying in industrial and commercial applications. These incandescent, gas-filled infrared heat lamps come up to full temperature almost immediately, eliminating costly warm-up time. Highly efficient heat generators produce a minimum of light rays and a high amount of infrared radiation. The BR40 lamp provides a built-in reflector for radiant energy control.

Product data

General Information		Approval and Application	
Cap-Base	E26 [Single Contact Medium Screw]	Approval Marks	Circle E logo
Operating Position	UNIVERSAL [Any or Universal (U)]	Product Data	
Rated Lifetime (Hours)	5,000 hour(s)	Order product name	250R40 IR/HR/TG 120V 4/1
Lighting Technology	Incandescent	Full product name	250R40 IR/HR/TG 120V 4/1
Operating and Electrical		Order code	159327
Power Consumption	250 W	Material Nr. (12NC)	925272736308
Voltage (Nom)	120 V	Numerator - Quantity Per Pack	1
Voltage (Nom)	120 V	EAN/UPC - Product/Case	046677159320
Mechanical and Housing		Numerator - Packs per outer box	4
Bulb Finish	Red	EAN/UPC - Case	50046677159325
Bulb Material	Hard Glass		
Bulb Shape	R40 (R40)		

Reflector Infrared R40

Dimensional drawing



Product	C (max)
250R40 IR/HR/TG 120V 4/1	6.875 inch

