



Silicone Coated Rough Service

100A/RS/TF 120-130V 60PK

The Philips Family of Silicone Coated Rough Service bulbs are the perfect choice in areas where there is concern if a bulb drops or shatters. Since Silicone Coated Rough Service bulbs resist breakage or shattering, they are perfect for food serving areas, as well as, standard, industrial rough surface, appliance and sign use.


Product data

| General Information | |
|--------------------------|-----------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime | 1,000 hour(s) |
| Rated Lifetime (Hours) | 1,000 hour(s) |
| Lighting Technology | Incandescent |
| Light Technical | |
| Luminous Flux | 1,050 lm |
| Operating and Electrical | |
| Power Consumption | 100 W |
| Starting Time (Nom) | 0.0 s |
| Voltage (Nom) | 120-130 V |

| Mechanical and Housing | |
|---------------------------------|--------------------------|
| Bulb Finish | Frost Silicone |
| Bulb Shape | A21 |
| Product Data | |
| Order product name | 100A/RS/TF 120-130V 60PK |
| Full product name | 100A/RS/TF 120-130V 60PK |
| Order code | 925286736303 |
| Material Nr. (12NC) | 925286736303 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677279851 |
| Numerator - Packs per outer box | 60 |
| EAN/UPC - Case | 50046677149715 |

Silicone Coated Rough Service

Dimensional drawing



| Product |
|--------------------------|
| 100A/RS/TF 120-130V 60PK |

