



Frost / Clear

150A 120V 48PK

The Philips Family of Standard Frost and Clear bulbs are good for everyday use. Clear bulbs provide sparkle, especially in fixtures that are made of chrome, have mirrored surfaces, multiple sockets or have cut glass parts. If glare is a problem, use a dimmer or a lower wattage bulb to reduce brightness. Clear bulbs are also used in fixtures with reflectors. Frost bulbs provide soft light with reduced glare.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	750 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	2,620 lumen
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	A21 [A 21mm]
Product Data	
Order product name	150A 120V 48PK
Order code	925287336306
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48
Material Nr. (12NC)	925287336306
Full product name	150A 120V 48PK
EAN/UPC - Case	50046677270037
EAN/UPC - Product/Case	046677270032

Frost / Clear

Dimensional drawing



Product	D	C (max)
150A 120V 48PK	2.625 inch	5.312 inch

